

Network Connectivity - Opto Splitter in Enclosure

Pathway Connectivity Opto Splitter in Enclosure



Opto-splitters for permanent installations, installed in NEMA-1 enclosures, complete with conduit knock-outs and terminal strip connections for fast, easy installation.

FEATURES

- Modules are mounted & pre-wired, ready to install
- Up to 4 eDIN 1002 opto-splitters (16 outputs total)
- Up to 4 inputs
- Direct pass-thru connectors
- No fuses, self resetting data links
- Termination switch
- 2500V opto-isolation input to output
- 250V fault protection on all DMX ports
- Wide range power supply (110-240VAC, 50/60Hz)
- Power, DMX present and transmit indicators

MODEL DESCRIPTION

- 4807 4 way eDIN Installation Repeater
- 4808 8 way eDIN Installation Repeater
- 4809 12 way eDIN Installation Repeater
- 4810 16 way eDIN Installation Repeater

SPECIFICATIONS


Power Supply UL listed, DIN rail, universal input 100-240 VAC, 50/60 Hz

Isolation

- 2500V opto-isolation input to output
- 250V fault protection

Sizes:

- 4807 & 4808 10.25" x 13.25" (260mm x 335mm)
- 4808 & 4809 10.25" x 23.25" (260mm x 509mm)



SPECIFICATIONS

eDIN 4808 Installation Repeater

ORDERING INFORMATION

Ordering Number	65-OSE01-001-00	4 Way Opto Splitter in enclosure
	65-OSE02-001-00	8 Way Opto Splitter in enclosure
	65-OSE03-001-00	12 Way Opto Splitter in enclosure
	65-OSE04-001-00	16 Way Opto Splitter in enclosure

Applications

- Dry location

Specification sheets are subject to change without notice. For the most recent version, please refer to www.ilight-tech.com.

Product Application

Hypnotica iS